




## Garras blandas extra anchas Paso 1.5 mm x 60°



| Modelo (6") | S-1 | S-2 | S-3 | S-4 | S-5 | S-6 | S-7 | S-8 | S-9 | S-10 | S-11 | Paso del dentado | Ángulo   | Peso bruto (kg) |
|-------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|------------------|----------|-----------------|
| GB0603048B  | 73  | 48  | 30  | 12  | 5   | 18  | 20  | 38  | M10 | 15   | 20   | 1.5x60°          | Estándar | 1.96            |
| GB0603060B  | 73  | 60  | 30  | 12  | 5   | 18  | 20  | 38  | M10 | 15   | 30   | 1.5x60°          | Estándar | 2.76            |
| GB0603080B  | 73  | 80  | 30  | 12  | 5   | 18  | 20  | 38  | M10 | 15   | 50   | 1.5x60°          | Estándar | 3.82            |
| GB0604848B  | 73  | 48  | 48  | 12  | 5   | 36  | 20  | 38  | M10 | 15   | 20   | 1.5x60°          | Estándar | 3.22            |
| GB0604863B  | 73  | 63  | 48  | 12  | 5   | 36  | 20  | 38  | M10 | 15   | 33   | 1.5x60°          | Estándar | 4.30            |
| GB0606060B  | 73  | 60  | 60  | 12  | 5   | 48  | 20  | 38  | M10 | 15   | 30   | 1.5x60°          | Estándar | 5.32            |
| GB0607070B  | 73  | 70  | 70  | 12  | 5   | 58  | 20  | 38  | M10 | 15   | 35   | 1.5x60°          | Estándar | 7.62            |

| Modelo (8") | S-1 | S-2 | S-3 | S-4 | S-5 | S-6 | S-7 | S-8 | S-9 | S-10 | S-11 | Paso del dentado | Ángulo   | Peso bruto (kg) |
|-------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|------------------|----------|-----------------|
| GB0803648B  | 95  | 48  | 36  | 14  | 5   | 21  | 25  | 46  | M12 | 24   | 20   | 1.5x60°          | Estándar | 3.42            |
| GB0803663B  | 95  | 63  | 36  | 14  | 5   | 21  | 25  | 46  | M12 | 24   | 33   | 1.5x60°          | Estándar | 4.48            |
| GB0803680B  | 95  | 80  | 36  | 14  | 5   | 21  | 25  | 46  | M12 | 24   | 50   | 1.5x60°          | Estándar | 5.86            |
| GB0804848B  | 95  | 48  | 48  | 14  | 5   | 33  | 25  | 46  | M12 | 24   | 20   | 1.5x60°          | Estándar | 4.26            |
| GB0804873B  | 95  | 73  | 48  | 14  | 5   | 33  | 25  | 46  | M12 | 24   | 35   | 1.5x60°          | Estándar | 6.94            |
| GB0804890B  | 95  | 90  | 48  | 14  | 5   | 33  | 25  | 46  | M12 | 24   | 50   | 1.5x60°          | Estándar | 8.96            |
| GB0806363B  | 95  | 63  | 63  | 14  | 5   | 48  | 25  | 46  | M12 | 24   | 30   | 1.5x60°          | Estándar | 7.44            |
| GB0807373B  | 95  | 73  | 73  | 14  | 5   | 58  | 25  | 46  | M12 | 24   | 35   | 1.5x60°          | Estándar | 10.52           |
| GB0808383B  | 95  | 83  | 83  | 14  | 5   | 68  | 25  | 46  | M12 | 24   | 45   | 1.5x60°          | Estándar | 12.38           |

| Modelo (10") | S-1 | S-2 | S-3 | S-4 | S-5 | S-6 | S-7 | S-8 | S-9 | S-10 | S-11 | Paso del dentado | Ángulo   | Peso bruto (kg) |
|--------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|------|------|------------------|----------|-----------------|
| GB1004263B   | 110 | 63  | 42  | 16  | 5   | 27  | 30  | 50  | M12 | 30   | 33   | 1.5x60°          | Estándar | 5.6             |
| GB10042100B  | 110 | 100 | 42  | 16  | 5   | 27  | 30  | 50  | M12 | 30   | 60   | 1.5x60°          | Estándar | 8.5             |
| GB1004873B   | 110 | 73  | 48  | 16  | 5   | 33  | 30  | 50  | M12 | 30   | 35   | 1.5x60°          | Estándar | 8.06            |
| GB1006363B   | 110 | 63  | 63  | 16  | 5   | 48  | 30  | 50  | M12 | 30   | 30   | 1.5x60°          | Estándar | 9.1             |
| GB1007373B   | 110 | 73  | 73  | 16  | 5   | 58  | 30  | 50  | M12 | 30   | 35   | 1.5x60°          | Estándar | 12.86           |
| GB1008383B   | 110 | 83  | 83  | 16  | 5   | 68  | 30  | 50  | M12 | 30   | 45   | 1.5x60°          | Estándar | 16.96           |